


Document overview

File name: 0052-20 BPRIM Katalog wersja xxx_____CONTENT__KORR.pdf
 Title: -
 Application: Adobe InDesign 20.2 (Macintosh)
 Producer: Adobe PDF Library 17.0
 Author: -
 Created on: 01/23/2026 03:52:02 PM
 Date Modified: 01/26/2026 09:31:44 AM
 File Size: 150.3 MByte / 153882.0 KByte
 Trapped: No
 Output Intent: -
 PDF/X Version: -
 PDF Version: 1.6
 Number of pages: 140
 MediaBox: 234.82 x 321.82 mm
 TrimBox: 210.00 x 297.00 mm



Summary

	✖ Error	⚠ Warning	✅ Fixed	ℹ Info
Document	-	-	-	-
PDF/X	-	-	-	-
Pages	-	-	-	-
Colors	-	826	-	-
Fonts	-	-	-	-
Images	-	182	98	-
Content	-	219	-	-

Colors

- ⚠ Maximum dot area 322% is above the 320% threshold #4 (36)
- ⚠ Maximum dot area 325% is above the 320% threshold #2 (39,75)
- ⚠ Maximum dot area 326% is above the 320% threshold #5 (36,112)
- ⚠ Maximum dot area 327% is above the 320% threshold #3 (112,128,136)
- ⚠ Maximum dot area 328% is above the 320% threshold #1 (117)
- ⚠ Maximum dot area 329% is above the 320% threshold #6 (12,36,68)
- ⚠ Maximum dot area 330% is above the 320% threshold #118 (5,11-12,14,20,22,25,34,38-40,44,49,52,57,59,61,66,68,73,75-77,82-83,93,96-97,101-102,105,110,112,114,117,119,129-131)
- ⚠ Maximum dot area 331% is above the 320% threshold #8 (5,29,34,46,112,117,122)
- ⚠ Maximum dot area 332% is above the 320% threshold #5 (24,26,29,98,117)
- ⚠ Maximum dot area 333% is above the 320% threshold #24 (5-6,18,33-34,36,38,47,57,69,75,89,101,117,122-123,134)
- ⚠ Maximum dot area 334% is above the 320% threshold #14 (14,40,50,73,75,88-89,101,103,111,124,129)
- ⚠ Maximum dot area 335% is above the 320% threshold #50 (5,8,13,25-27,29,34,38-40,47,50,56,58,60,66,69-71,73,76,85,87,89,98-99,112-113,116-117,120,124,134)

- ⚠ Maximum dot area 336% is above the 320% threshold #64 (5-6,11,14-15,24,26,28,39,42-43,46-49,51-52,56-58,60,66,69,72-73,77,86,98,101,103-104,106,111-113,115-117,129,131,134,137)
- ⚠ Maximum dot area 337% is above the 320% threshold #62 (5,7-8,11,13-15,17,21,25,27,34,36,39,41,46,50-51,60,62,68,71-73,83,85,91,96-98,101,103,111-112,114-115,117,124,129,131,134)
- ⚠ Maximum dot area 338% is above the 320% threshold #113 (5-9,11,13,17,19-21,24-28,30,39,41-43,46-47,49-50,53,58,60,62,70,73,75,84,86-90,93,98,100-101,108-111,113,115-117,122,124-125,129,131,133-134)
- ⚠ Maximum dot area 339% is above the 320% threshold #69 (5-8,11,13,20-22,25,28-29,33,39-42,46,66-67,69-71,73,79,86-87,94,96,98,100-101,110,112-113,116-117,125,131,134)
- ⚠ Maximum dot area 340% is above the 320% threshold #74 (2,6-11,16-17,20,24-30,34,39-40,43,47-49,55-56,58,67,72,75,82,87,89,91,94-96,103,106,110,113-116,119,124-125,129-131,134)
- ⚠ Maximum dot area 341% is above the 320% threshold #33 (6-8,10,15,17,24-26,29,36,40-41,45,47,49,56-57,82,87,91,96,99,104,116,119,126,130)
- ⚠ Maximum dot area 342% is above the 320% threshold #39 (3,7,9,11,18,21,24-25,27,40-41,48,56,64,66-67,70,73,77,85,90-91,93,98-99,110,116,118-120,127-128)
- ⚠ Maximum dot area 343% is above the 320% threshold #10 (34,38,46,48,81,85,121,123,126,132)
- ⚠ Maximum dot area 344% is above the 320% threshold #10 (24,31,90,109-110,118,126,137)
- ⚠ Maximum dot area 345% is above the 320% threshold #7 (36,53,92,130)
- ⚠ Maximum dot area 347% is above the 320% threshold #2 (32,37)
- ⚠ Maximum dot area 348% is above the 320% threshold #1 (23)
- ⚠ Maximum dot area 349% is above the 320% threshold #9 (7,36,38,54,84,133)
- ⚠ Maximum dot area 350% is above the 320% threshold #1 (51)
- ⚠ Maximum dot area 351% is above the 320% threshold #2 (69,86)
- ⚠ Maximum dot area 352% is above the 320% threshold #2 (7,27)
- ⚠ Maximum dot area 353% is above the 320% threshold #2 (38)
- ⚠ Maximum dot area 355% is above the 320% threshold #2 (123,138)
- ⚠ Maximum dot area 356% is above the 320% threshold #1 (38)
- ⚠ Maximum dot area 358% is above the 320% threshold #2 (17,58)
- ⚠ Maximum dot area 359% is above the 320% threshold #1 (85)
- ⚠ Maximum dot area 361% is above the 320% threshold #2 (138)
- ⚠ Maximum dot area 363% is above the 320% threshold #1 (89)
- ⚠ Maximum dot area 364% is above the 320% threshold #1 (85)
- ⚠ Maximum dot area 365% is above the 320% threshold #2 (138)
- ⚠ Maximum dot area 366% is above the 320% threshold #1 (109)
- ⚠ Maximum dot area 371% is above the 320% threshold #1 (96)
- ⚠ Maximum dot area 392% is above the 320% threshold #1 (6)
- ⚠ Maximum dot area 394% is above the 320% threshold #1 (74)
- ⚠ Maximum dot area 400% is above the 320% threshold #2 (2,109)
- ⚠ 4-color CMYK Black - 68.4 67.8 62.8 80.0 #4 (36)
- ⚠ 4-color CMYK Black - 69.4 68.8 63.7 81.1 #4 (36)

- ⚠ 4-color CMYK Black - 70.3 69.7 64.6 82.2 #4 (36)
- ⚠ 4-color CMYK Black - 71.3 70.6 65.4 83.3 #4 (36)
- ⚠ 4-color CMYK Black - 72.2 71.6 66.3 84.4 #4 (36)
- ⚠ 4-color CMYK Black - 73.2 72.5 67.2 85.6 #4 (36)
- ⚠ 4-color CMYK Black - 74.1 73.5 68.0 86.7 #4 (36)
- ⚠ 4-color CMYK Black - 75.1 74.4 68.9 87.8 #4 (36)
- ⚠ 4-color CMYK Black - 76.0 75.3 69.8 88.9 #4 (36)
- ⚠ 4-color CMYK Black - 77.0 76.3 70.7 90.0 #4 (36)
- ⚠ 4-color CMYK Black - 77.9 77.2 71.5 91.1 #4 (36)
- ⚠ 4-color CMYK Black - 78.9 78.2 72.4 92.2 #4 (36)
- ⚠ 4-color CMYK Black - 79.8 79.1 73.3 93.3 #4 (36)
- ⚠ 4-color CMYK Black - 80.8 80.1 74.2 94.4 #4 (36)
- ⚠ 4-color CMYK Black - 81.7 81.0 75.0 95.6 #4 (36)
- ⚠ 4-color CMYK Black - 82.7 81.9 75.9 96.7 #4 (36)
- ⚠ 4-color CMYK Black - 83.6 82.9 76.8 97.8 #4 (36)

Images

- ⚠ Color image resolution 60 dpi is below 260 dpi #1 (63)
- ⚠ Color image resolution 63 dpi is below 260 dpi #1 (65)
- ⚠ Color image resolution 71 dpi is below 260 dpi #1 (54)
- ⚠ Color image resolution 80 dpi is below 260 dpi #1 (129)
- ⚠ Color image resolution 83 dpi is below 260 dpi #1 (83)
- ⚠ Color image resolution 84 dpi is below 260 dpi #1 (83)
- ⚠ Color image resolution 90 dpi is below 260 dpi #1 (102)
- ⚠ Color image resolution 93 dpi is below 260 dpi #1 (83)
- ⚠ Color image resolution 99 dpi is below 260 dpi #3 (83)
- ⚠ Color image resolution 100 dpi is below 260 dpi #1 (83)
- ⚠ Color image resolution 101 dpi is below 260 dpi #22 (83,128,138)
- ⚠ Color image resolution 102 dpi is below 260 dpi #6 (83,128,138)
- ⚠ Color image resolution 104 dpi is below 260 dpi #3 (83,94)
- ⚠ Color image resolution 107 dpi is below 260 dpi #1 (130)
- ⚠ Color image resolution 109 dpi is below 260 dpi #4 (4,83)
- ⚠ Color image resolution 110 dpi is below 260 dpi #3 (83)
- ⚠ Color image resolution 114 dpi is below 260 dpi #3 (10,114)
- ⚠ Color image resolution 115 dpi is below 260 dpi #1 (8)
- ⚠ Color image resolution 117 dpi is below 260 dpi #1 (8)
- ⚠ Color image resolution 121 dpi is below 260 dpi #1 (8)
- ⚠ Color image resolution 127 dpi is below 260 dpi #11 (79)
- ⚠ Color image resolution 129 dpi is below 260 dpi #2 (112,114)
- ⚠ Color image resolution 130 dpi is below 260 dpi #1 (11)
- ⚠ Color image resolution 131 dpi is below 260 dpi #1 (39)
- ⚠ Color image resolution 138 dpi is below 260 dpi #1 (43)
- ⚠ Color image resolution 139 dpi is below 260 dpi #1 (112)
- ⚠ Color image resolution 140 dpi is below 260 dpi #1 (129)
- ⚠ Color image resolution 146 dpi is below 260 dpi #1 (10)
- ⚠ Color image resolution 149 dpi is below 260 dpi #1 (11)
- ⚠ Color image resolution 151 dpi is below 260 dpi #1 (11)

- ⚠ Color image resolution 154 dpi is below 260 dpi #1 (109)
- ⚠ Color image resolution 156 dpi is below 260 dpi #12 (79,130)
- ⚠ Color image resolution 163 dpi is below 260 dpi #2 (24,93)
- ⚠ Color image resolution 164 dpi is below 260 dpi #1 (113)
- ⚠ Color image resolution 172 dpi is below 260 dpi #1 (122)
- ⚠ Color image resolution 177 dpi is below 260 dpi #1 (8)
- ⚠ Color image resolution 179 dpi is below 260 dpi #1 (129)
- ⚠ Color image resolution 182 dpi is below 260 dpi #3 (10,129)
- ⚠ Color image resolution 183 dpi is below 260 dpi #1 (129)
- ⚠ Color image resolution 184 dpi is below 260 dpi #1 (79)
- ⚠ Color image resolution 186 dpi is below 260 dpi #1 (43)
- ⚠ Color image resolution 187 dpi is below 260 dpi #1 (79)
- ⚠ Color image resolution 190 dpi is below 260 dpi #2 (5,11)
- ⚠ Color image resolution 192 dpi is below 260 dpi #3 (79,81,109)
- ⚠ Color image resolution 193 dpi is below 260 dpi #1 (79)
- ⚠ Color image resolution 196 dpi is below 260 dpi #2 (51,79)
- ⚠ Color image resolution 199 dpi is below 260 dpi #1 (9)
- ⚠ Color image resolution 200 dpi is below 260 dpi #1 (9)
- ⚠ Color image resolution 202 dpi is below 260 dpi #1 (89)
- ⚠ Color image resolution 209 dpi is below 260 dpi #1 (113)
- ⚠ Color image resolution 213 dpi is below 260 dpi #3 (24,59,64)
- ⚠ Color image resolution 214 dpi is below 260 dpi #4 (11)
- ⚠ Color image resolution 216 dpi is below 260 dpi #1 (125)
- ⚠ Color image resolution 217 dpi is below 260 dpi #1 (79)
- ⚠ Color image resolution 219 dpi is below 260 dpi #3 (11,44,130)
- ⚠ Color image resolution 220 dpi is below 260 dpi #1 (101)
- ⚠ Color image resolution 221 dpi is below 260 dpi #3 (71,84,133)
- ⚠ Color image resolution 222 dpi is below 260 dpi #5 (117,130)
- ⚠ Color image resolution 225 dpi is below 260 dpi #1 (114)
- ⚠ Color image resolution 226 dpi is below 260 dpi #2 (31,117)
- ⚠ Color image resolution 227 dpi is below 260 dpi #3 (95,117)
- ⚠ Color image resolution 228 dpi is below 260 dpi #3 (117)
- ⚠ Color image resolution 229 dpi is below 260 dpi #6 (117)
- ⚠ Color image resolution 231 dpi is below 260 dpi #4 (8,14,21,100)
- ⚠ Color image resolution 232 dpi is below 260 dpi #1 (117)
- ⚠ Color image resolution 234 dpi is below 260 dpi #1 (11)
- ⚠ Color image resolution 235 dpi is below 260 dpi #1 (30)
- ⚠ Color image resolution 236 dpi is below 260 dpi #1 (3)
- ⚠ Color image resolution 239 dpi is below 260 dpi #1 (11)
- ⚠ Color image resolution 240 dpi is below 260 dpi #3 (12,40,113)
- ⚠ Color image resolution 243 dpi is below 260 dpi #3 (83)
- ⚠ Color image resolution 245 dpi is below 260 dpi #2 (11)
- ⚠ Color image resolution 246 dpi is below 260 dpi #1 (37)
- ⚠ Color image resolution 247 dpi is below 260 dpi #1 (71)
- ⚠ Color image resolution 249 dpi is below 260 dpi #1 (109)
- ⚠ Color image resolution 252 dpi is below 260 dpi #3 (75,85,115)

- ⚠ Color image resolution 253 dpi is below 260 dpi #1 (101)
- ⚠ Color image resolution 254 dpi is below 260 dpi #1 (76)
- ⚠ Color image resolution 255 dpi is below 260 dpi #1 (41)
- ⚠ Color image resolution 256 dpi is below 260 dpi #1 (101)
- ⚠ Color image resolution 257 dpi is below 260 dpi #1 (112)
- ⚠ Color image resolution 258 dpi is below 260 dpi #2 (51,92)
- ✅ Image is indexed - Color space: Device CMYK #98 (2,11,14,22,25,29,38-40,49,52,59,66,68,73,75-77,79-80,83,85,96-98,101,104-109,116,118,130-131,134)

Content

- ⚠ Line weight 0.015 mm is below hairline threshold 0.076 mm #1 (128)
- ⚠ Line weight 0.028 mm is below hairline threshold 0.076 mm #1 (138)
- ⚠ Line weight 0.032 mm is below hairline threshold 0.076 mm #1 (79)
- ⚠ Line weight 0.037 mm is below hairline threshold 0.076 mm #3 (83)
- ⚠ Line weight 0.041 mm is below hairline threshold 0.076 mm #2 (131)
- ⚠ Line weight 0.048 mm is below hairline threshold 0.076 mm #5 (73)
- ⚠ Line weight 0.049 mm is below hairline threshold 0.076 mm #3 (79)
- ⚠ Line weight 0.060 mm is below hairline threshold 0.076 mm #1 (128)
- ⚠ Line weight 0.061 mm is below hairline threshold 0.076 mm #2 (79,135)
- ⚠ Line weight 0.065 mm is below hairline threshold 0.076 mm #7 (79)
- ⚠ Line weight 0.071 mm is below hairline threshold 0.076 mm #147 (3,5,7,9,11,13,15,17,19,21,23,25,27,29,31,33,35,37,39,41,43,45,47,49,51,53,55,57,59,61,63,65,67,69,71,73,75,77,79,81,83,85,87,89,91,93,95,97,99,101,103,105,107,109,111,113,115,117,119,121,123,125,127,129,131,133,135,137)
- ⚠ Line weight 0.072 mm is below hairline threshold 0.076 mm #22 (24,61)
- ⚠ Line weight 0.074 mm is below hairline threshold 0.076 mm #9 (83)
- ⚠ Line weight 0.000 mm is below hairline threshold 0.010 mm #15 (79,126,131)

Additional information


Settings used: Qualify_1

Color separations: 5

 CMYK

 PANTONE Black C

Page 1 - 126 

Page 127 - 140 

Color spaces

📄 DeviceCMYK / DeviceGray / Separation / DeviceN

Fonts: 392

📄 Aharoni,Bold

TrueType / WinAnsi / embedded subset

📄 Arial-BoldMT

TrueType / WinAnsi / embedded subset

📄 Arial-BoldMT

TrueType (CID) / Identity-H / embedded subset

📄 Arial-ItalicMT

TrueType / WinAnsi / embedded subset

📄 ArialBlack

TrueType (CID) / Identity-H / embedded subset

📄 ArialMT

TrueType / WinAnsi / embedded subset

① ArialMT (3x)	TrueType (CID) / Identity-H / embedded subset
① ArialMT	Type1 / Custom / embedded subset
① ArialMTStd (3x)	Type1 / Custom / embedded subset
① ArialMTStd-Light (3x)	Type1 / Custom / embedded subset
① ArialMTStd-Medium (2x)	Type1 / Custom / embedded subset
① ArialRoundedMTPro (5x)	Type1 (CID) / Identity-H / embedded subset
① ArialRoundedMTPro (4x)	Type1 / Custom / embedded subset
① ArialRoundedMTPro-Light (3x)	Type1 (CID) / Identity-H / embedded subset
① ArialRoundedMTPro-Light (4x)	Type1 / Custom / embedded subset
① ArialRoundedMTStd (2x)	Type1 / Custom / embedded subset
① CIDFont+F1 (2x)	TrueType / WinAnsi / embedded subset
① CIDFont+F1	TrueType (CID) / Identity-H / embedded subset
① CIDFont+F2	TrueType / WinAnsi / embedded subset
① CIDFont+F2 (3x)	TrueType (CID) / Identity-H / embedded subset
① CIDFont+F3 (2x)	TrueType (CID) / Identity-H / embedded subset
① CIDFont+F4 (2x)	TrueType (CID) / Identity-H / embedded subset
① CIDFont+F5	TrueType / WinAnsi / embedded subset
① CIDFont+F5	TrueType (CID) / Identity-H / embedded subset
① Calibri (9x)	TrueType / WinAnsi / embedded subset
① Calibri (2x)	TrueType (CID) / Identity-H / embedded subset
① Calibri,Bold	TrueType (CID) / Identity-H / embedded subset
① Calibri-Bold (9x)	TrueType / WinAnsi / embedded subset
① Calibri-Bold (2x)	TrueType (CID) / Identity-H / embedded subset
① Calibri-Italic	TrueType / WinAnsi / embedded subset
① CenturyGothic	TrueType / WinAnsi / embedded subset
① CenturyGothic-Bold	TrueType / WinAnsi / embedded subset
① DINOT (2x)	Type1 (CID) / Identity-H / embedded subset
① DejaVuSans (7x)	TrueType / WinAnsi / embedded subset
① DejaVuSans-Bold (7x)	TrueType / WinAnsi / embedded subset
① Eurostile-DemiOblique	Type1 / WinAnsi / embedded subset
① Garet-Bold (60x)	TrueType / WinAnsi / embedded subset
① Garet-ExtraBold (2x)	TrueType / WinAnsi / embedded subset
① Garet-Regular (50x)	TrueType (CID) / Identity-H / embedded subset
① GraphSchneider-Regular (2x)	Type1 / Custom / embedded subset
① Helvetica (11x)	TrueType / WinAnsi / embedded subset
① Helvetica (2x)	TrueType (CID) / Identity-H / embedded subset
① Helvetica (3x)	Type1 / Custom / embedded subset
① Helvetica-Bold	TrueType / WinAnsi / embedded subset
① HelveticaNeue-BlackCond	Type1 / WinAnsi / embedded subset
① HelveticaNeue-BoldCond	Type1 / WinAnsi / embedded subset
① HelveticaNeue-BoldCondObl	Type1 / WinAnsi / embedded subset
① HelveticaNeue-BoldItalic	Type1 / Custom / embedded subset
① HelveticaNeue-ExtBlackCond	Type1 / WinAnsi / embedded subset
① HelveticaNeue-LightCondObl	Type1 / WinAnsi / embedded subset
① HelveticaNeueLTStd-BdCn	Type1 / WinAnsi / embedded subset
① HelveticaNeueLTStd-Cn	Type1 / Custom / embedded subset

① HelveticaNeueLTW1G-Bd (3x)	Type1 / Custom / embedded subset
① HelveticaNeueLTW1G-Roman (3x)	Type1 / Custom / embedded subset
① KaufmannBT-Bold	TrueType / WinAnsi / embedded subset
① Lexend-Bold	TrueType / WinAnsi / embedded subset
① Lexend-Bold	TrueType (CID) / Identity-H / embedded subset
① Lexend-Light	TrueType / WinAnsi / embedded subset
① Lexend-Medium	TrueType / WinAnsi / embedded subset
① Lexend-Regular	TrueType / WinAnsi / embedded subset
① Lexend-SemiBold	TrueType / WinAnsi / embedded subset
① MinionPro-Regular	Type1 / WinAnsi / embedded subset
① MontserratUnderline-SemiBold	TrueType / WinAnsi / embedded subset
① MuseoSans-100	Type1 / Custom / embedded subset
① MuseoSans-300Italic	Type1 / WinAnsi / embedded subset
① MuseoSans-500	Type1 / Custom / embedded subset
① MyriadPro-Regular	Type1 / Custom / embedded subset
① OpenSans-Bold (2x)	TrueType / WinAnsi / embedded subset
① OpenSans-Bold (2x)	TrueType (CID) / Identity-H / embedded subset
① OpenSans-Light (2x)	TrueType / WinAnsi / embedded subset
① PlusJakartaSans-Bold	Type1 / Custom / embedded subset
① PlusJakartaSans-Regular	Type1 / Custom / embedded subset
① Roboto-Black	TrueType / WinAnsi / embedded subset
① Roboto-Bold (20x)	TrueType / WinAnsi / embedded subset
① Roboto-Bold (6x)	TrueType (CID) / Identity-H / embedded subset
① Roboto-Italic (2x)	TrueType / WinAnsi / embedded subset
① Roboto-Light (16x)	TrueType / WinAnsi / embedded subset
① Roboto-Light (7x)	TrueType (CID) / Identity-H / embedded subset
① Roboto-Medium (13x)	TrueType / WinAnsi / embedded subset
① Roboto-Medium	TrueType (CID) / Identity-H / embedded subset
① Roboto-Regular (21x)	TrueType / WinAnsi / embedded subset
① Roboto-Regular	TrueType (CID) / Identity-H / embedded subset
① Roboto-Thin	TrueType / WinAnsi / embedded subset
① RobotoCondensed-Bold (15x)	TrueType / WinAnsi / embedded subset
① RobotoCondensed-Bold	TrueType (CID) / Identity-H / embedded subset
① RobotoCondensed-Italic (6x)	TrueType / WinAnsi / embedded subset
① RobotoCondensed-Light	TrueType / WinAnsi / embedded subset
① RobotoCondensed-Regular (16x)	TrueType / WinAnsi / embedded subset
① RobotoCondensed-Regular (3x)	TrueType (CID) / Identity-H / embedded subset
① UtopiaStd-BlackHeadline	Type1 / WinAnsi / embedded subset
① VAG-Rounded-Bold	TrueType / WinAnsi / embedded subset
① Wingdings3	Type1 / Custom / embedded subset