


Document overview

File name: 1425 Socomec CONTENT.pdf
 Title: DCG0001505it_cataloguepc0.indb
 Application: Adobe InDesign 18.3 (Windows)
 Producer: Acrobat Distiller 23.0 (Windows)
 Author: HLN
 Created on: 03/07/2024 01:53:28 PM
 Date Modified: 10/28/2025 12:15:54 PM
 File Size: 143.7 MByte / 147135.8 KByte
 Trapped: Unknown
 Output Intent: -
 PDF/X Version: -
 PDF Version: 1.6
 Number of pages: 124
 MediaBox: 208.00 x 287.00 mm
 TrimBox: 187.95 x 265.81 mm



Summary

	✖ Error	⚠ Warning	✅ Fixed	ℹ Info
📄 Document	-	-	-	-
📄 PDF/X	-	-	-	-
📄 Pages	-	-	-	-
⚠ Colors	-	530	-	-
📄 Fonts	-	-	-	-
⚠ Images	-	490	232	-
📄 Content	-	-	-	-

Colors

- ⚠ Maximum dot area 325% is above the 320% threshold #2 (34,69)
- ⚠ Maximum dot area 327% is above the 320% threshold #7 (18,46-47,72,82)
- ⚠ Maximum dot area 328% is above the 320% threshold #7 (53,71)
- ⚠ Maximum dot area 329% is above the 320% threshold #21 (21,34,71-72,100)
- ⚠ Maximum dot area 330% is above the 320% threshold #6 (18,20,44,47,102)
- ⚠ Maximum dot area 331% is above the 320% threshold #6 (13,44,46-47,84,103)
- ⚠ Maximum dot area 332% is above the 320% threshold #4 (44,47)
- ⚠ Maximum dot area 333% is above the 320% threshold #15 (18,30,34,38,44,72,111)
- ⚠ Maximum dot area 334% is above the 320% threshold #6 (16,18,44,46,107)
- ⚠ Maximum dot area 335% is above the 320% threshold #15 (18,20,28,44,46-47,93)
- ⚠ Maximum dot area 336% is above the 320% threshold #26 (18,28,38,44,46-47,52,65,73-74,82-83,103)
- ⚠ Maximum dot area 337% is above the 320% threshold #8 (18,28,36,43,46-47,93)
- ⚠ Maximum dot area 338% is above the 320% threshold #10 (13,18,28,44,73,104)
- ⚠ Maximum dot area 339% is above the 320% threshold #24 (2,18,28,44,47,73-74,101)
- ⚠ Maximum dot area 340% is above the 320% threshold #20 (13,16,18,20,28,30,44,58,72-74,108)
- ⚠ Maximum dot area 341% is above the 320% threshold #12 (18,28,30,42,44,47,52,78,83)
- ⚠ Maximum dot area 342% is above the 320% threshold #8 (28,30,47,73,83)

- ⚠ Maximum dot area 343% is above the 320% threshold #4 (28,30,83)
- ⚠ Maximum dot area 344% is above the 320% threshold #12 (16,28,30,36,47,69,73,75,110)
- ⚠ Maximum dot area 345% is above the 320% threshold #16 (13,30,46-47,57,66,73,83,109)
- ⚠ Maximum dot area 346% is above the 320% threshold #6 (28,65,73,78)
- ⚠ Maximum dot area 347% is above the 320% threshold #15 (4,28,30,43,46-47,73,78,83)
- ⚠ Maximum dot area 348% is above the 320% threshold #7 (1,28,47,73,102)
- ⚠ Maximum dot area 349% is above the 320% threshold #45 (9,30,34,73,91,117,119-120)
- ⚠ Maximum dot area 350% is above the 320% threshold #13 (9,28,46,73,83-84,105)
- ⚠ Maximum dot area 351% is above the 320% threshold #9 (28,34,47,52,73,83)
- ⚠ Maximum dot area 352% is above the 320% threshold #4 (20,73,78)
- ⚠ Maximum dot area 353% is above the 320% threshold #2 (38,47)
- ⚠ Maximum dot area 354% is above the 320% threshold #2 (28,73)
- ⚠ Maximum dot area 355% is above the 320% threshold #3 (60,78,109)
- ⚠ Maximum dot area 356% is above the 320% threshold #3 (10,38,65)
- ⚠ Maximum dot area 357% is above the 320% threshold #6 (3,30,38,64,88-89)
- ⚠ Maximum dot area 358% is above the 320% threshold #3 (44,73,92)
- ⚠ Maximum dot area 360% is above the 320% threshold #10 (22-23,29,32,46,53,57,59,79)
- ⚠ Maximum dot area 361% is above the 320% threshold #7 (14,23,29,32,53,57,79)
- ⚠ Maximum dot area 362% is above the 320% threshold #7 (11,23,29,32,53,57,79)
- ⚠ Maximum dot area 363% is above the 320% threshold #4 (1,13,22,37)
- ⚠ Maximum dot area 364% is above the 320% threshold #5 (1,20,46,59,65)
- ⚠ Maximum dot area 365% is above the 320% threshold #4 (1,22,37,46)
- ⚠ Maximum dot area 366% is above the 320% threshold #1 (21)
- ⚠ Maximum dot area 367% is above the 320% threshold #5 (2,22,65,78)
- ⚠ Maximum dot area 369% is above the 320% threshold #4 (5,22,37)
- ⚠ Maximum dot area 371% is above the 320% threshold #8 (22,30,37,46,59,68)
- ⚠ Maximum dot area 372% is above the 320% threshold #5 (4,46,70,73,109)
- ⚠ Maximum dot area 373% is above the 320% threshold #6 (22,37,70,73)
- ⚠ Maximum dot area 374% is above the 320% threshold #1 (37)
- ⚠ Maximum dot area 376% is above the 320% threshold #2 (22,73)
- ⚠ Maximum dot area 380% is above the 320% threshold #3 (10,32,37)
- ⚠ Maximum dot area 381% is above the 320% threshold #2 (10,37)
- ⚠ Maximum dot area 382% is above the 320% threshold #3 (14,50,109)
- ⚠ Maximum dot area 383% is above the 320% threshold #3 (52,76,78)
- ⚠ Maximum dot area 387% is above the 320% threshold #3 (46,59,83)
- ⚠ Maximum dot area 389% is above the 320% threshold #2 (30,59)
- ⚠ Maximum dot area 390% is above the 320% threshold #1 (73)
- ⚠ Maximum dot area 392% is above the 320% threshold #1 (30)
- ⚠ Maximum dot area 394% is above the 320% threshold #1 (59)
- ⚠ Maximum dot area 398% is above the 320% threshold #1 (8)
- ⚠ Maximum dot area 400% is above the 320% threshold #3 (1,43,48)
- ⚠ 4-color CMYK Black - 69.5 66.8 63.7 83.2 #10 (105)
- ⚠ 4-color CMYK Black - 70.7 71.5 72.3 81.6 #11 (63)
- ⚠ 4-color CMYK Black - 74.4 64.8 62.9 81.3 #1 (9)

- ⚠ 4-color CMYK Black - 74.5 65.2 62.2 81.4 #10 (71)
- ⚠ 4-color CMYK Black - 74.6 65.2 61.7 81.3 #3 (71,101)
- ⚠ 4-color CMYK Black - 78.5 72.7 57.8 81.6 #2 (79)
- ⚠ 4-color CMYK Black - 79.0 72.8 58.0 81.7 #32 (67,69,101)
- ⚠ 4-color CMYK Black - 90.6 78.5 61.7 96.9 #3 (53)
- ⚠ 4-color CMYK Black - 91.0 78.5 61.7 97.3 #14 (34,71)
- ⚠ 4-color CMYK Black - 91.2 78.4 60.6 94.6 #1 (69)
- ⚠ 4-color CMYK Black - 91.2 78.8 62.0 97.5 #4 (21)

Images

- ⚠ Color image resolution 162 dpi is below 260 dpi #22 (30,46,63,67,69,71,80,94)
- ⚠ Color image resolution 163 dpi is below 260 dpi #94 (30,46,49,59,63,67,69,71,73,94)
- ⚠ Color image resolution 164 dpi is below 260 dpi #20 (9,30,46,49,63,67,69,73,94)
- ⚠ Color image resolution 165 dpi is below 260 dpi #65 (9,22,30,46,49,63,67,69,71,73,83,94)
- ⚠ Color image resolution 166 dpi is below 260 dpi #54 (9,22,30,46,49,63,67,69,71,73,80,83,94,101)
- ⚠ Color image resolution 167 dpi is below 260 dpi #94 (9,22,30,46,49,63,67,69,71,73,83,91,93-94)
- ⚠ Color image resolution 168 dpi is below 260 dpi #18 (22,30,32,37,49,59,67,69,71,80)
- ⚠ Color image resolution 204 dpi is below 260 dpi #1 (37)
- ⚠ Color image resolution 211 dpi is below 260 dpi #11 (67,69,71,73)
- ⚠ Color image resolution 216 dpi is below 260 dpi #2 (110-111)
- ⚠ Color image resolution 217 dpi is below 260 dpi #75 (30,46,49,67,69,71,73,83)
- ⚠ Color image resolution 220 dpi is below 260 dpi #3 (30,71,80)
- ⚠ Color image resolution 221 dpi is below 260 dpi #10 (30,71,73)
- ⚠ Color image resolution 222 dpi is below 260 dpi #5 (30,71,73)
- ⚠ Color image resolution 223 dpi is below 260 dpi #10 (30,46,49,69,105)
- ⚠ Color image resolution 231 dpi is below 260 dpi #1 (65)
- ⚠ Color image resolution 240 dpi is below 260 dpi #1 (65)
- ⚠ Color image resolution 243 dpi is below 260 dpi #2 (88-89)
- ⚠ Color image resolution 256 dpi is below 260 dpi #2 (64-65)
- ✅ Image is indexed - Color space: Device CMYK #232 (1,9,17-18,21-23,25,27-28,30-32,35,37,40,42,44,46-47,49,54,59,63,65,67,69,71-74,78,80,83,86,90-91,93-94,97,101,105,109,120)

Additional information

Settings used: Qualify_1

Color separations: 4

 CMYK

Color spaces

📄 DeviceCMYK / Separation / DeviceN

Fonts: 227

① Arial-BoldMT (3x)	TrueType / WinAnsi / embedded subset
① ArialMT	TrueType / WinAnsi / embedded subset
① GillSansMT-Bold	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-Bd	TrueType / MacRoman / embedded subset
① HelveticaNeueLTCom-Bd	Type1 / WinAnsi / embedded subset
① HelveticaNeueLTCom-Bd (33x)	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-Bd-Identity-H	Type1 (CID) / Identity-H / embedded subset
① HelveticaNeueLTCom-BdCn (13x)	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-BdIt	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-Blk (13x)	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-Cn (8x)	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-Cn	TrueType (CID) / Identity-H / embedded subset
① HelveticaNeueLTCom-Ex	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-Hv	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-HvCn (2x)	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-HvEx (3x)	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-HvEx-Identity-H	Type1 (CID) / Identity-H / embedded subset
① HelveticaNeueLTCom-It (2x)	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-Lt	TrueType / MacRoman / embedded subset
① HelveticaNeueLTCom-Lt (35x)	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-Lt (4x)	TrueType (CID) / Identity-H / embedded subset
① HelveticaNeueLTCom-Lt-Identity-H	Type1 (CID) / Identity-H / embedded subset
① HelveticaNeueLTCom-LtCn (2x)	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-LtIt (7x)	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-LtIt	TrueType (CID) / Identity-H / embedded subset
① HelveticaNeueLTCom-Md (2x)	TrueType (CID) / Identity-H / embedded subset
① HelveticaNeueLTCom-Roman	Type1 / MacRoman / embedded subset
① HelveticaNeueLTCom-Roman (50x)	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTCom-Roman	TrueType (CID) / Identity-H / embedded subset
① HelveticaNeueLTCom-Roman-Identity-H	Type1 (CID) / Identity-H / embedded subset
① HelveticaNeueLTCom-ThCn	TrueType / WinAnsi / embedded subset
① HelveticaNeueLTW1G-Bd	Type1 / Custom / embedded subset
① HelveticaNeueLTW1G-BdCn	Type1 / Custom / embedded subset
① HelveticaNeueLTW1G-Blk	Type1 / Custom / embedded subset
① HelveticaNeueLTW1G-Cn	Type1 / Custom / embedded subset
① HelveticaNeueLTW1G-Hv	Type1 / Custom / embedded subset
① HelveticaNeueLTW1G-It	Type1 / Custom / embedded subset
① HelveticaNeueLTW1G-Lt	Type1 / Custom / embedded subset
① HelveticaNeueLTW1G-LtCn	Type1 / Custom / embedded subset
① HelveticaNeueLTW1G-MdCn	Type1 / Custom / embedded subset

① HelveticaNeueLTW1G-Roman	Type1 / Custom / embedded subset
① MicrogrammaD-BoldExte	Type1 / Custom / embedded subset
① MicrogrammaD-MediExte	Type1 / Custom / embedded subset
① MicrosoftYaHeiUI-GBK-EUC-H	TrueType (CID) / Identity-H / embedded subset
① MicrosoftYaHeiUILight	TrueType (CID) / Identity-H / embedded subset
① MinionPro-Regular	Type1 / Custom / embedded subset
① MyriadPro-Regular	Type1 / Custom / embedded subset
① OptimaLT	TrueType / WinAnsi / embedded subset
① OptimaLT-BoldItalic (8x)	TrueType / WinAnsi / embedded subset
① OptimaLTStd-BoldItalic (2x)	Type1 / WinAnsi / embedded subset
① OptimaLTStd-BoldItalic (4x)	Type1 / Custom / embedded subset
① Symbol	Type1 / Custom / embedded subset
① SymbolMT	TrueType (CID) / Identity-H / embedded subset